



4 in. Round Ceiling Rated Fan Pan, 1/2 in. Depth, Five 1/2 in. KO's

By Raco
Catalog # 295-1

4 in. Round Ceiling Rated Fan Pan, 1/2 in. Depth, Five 1/2 in. KO's



Features

- Steel construction
- No protruding ground screw or fan mounting screws allows easy installation
- Metal protection plate eliminates debris or damage to wiring
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Maximum support load for ceiling fans 70 lbs. and 150 lbs. for static light fixtures
- Supplied with five 1/2 in. knockouts
- Easy to follow instructions and mounting hardware included
- 6.0 cu. in. capacity

General

Ceiling Fan Rated	Yes
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Ceiling;Light
Knockouts	1/2 in
Material	Steel
Size	4 in
Type	Ceiling Pan
UPC	050169902950

Dimensions

Actual Depth	0.88 in
Ceiling Fan Lbs.	70 lb
Cubic Capacity	6 cu.in
Depth	0.5 in
Fixture Lbs.	150 lb
Height	4.13 in
Raised Ground	Yes
Weight	0.58 lb
Width	4.13 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	10
Packaging Type	Box
Pallet Quantity	3200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Installation Manuals - Ceiling Box Installation Instructions](#)
[Installation Manuals - Installation Instructions for 295, 295-1 & 295XL](#)
[Sales Drawings - 295](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Sell Sheets - RACO® Ceiling Fan Boxes](#)
[Sell Sheets - 4 in. Round Ceiling Fan-Rated Support Pan](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: Choosing the Correct Ceiling Fan Box](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-2951-SPEC-EN | REV 6/2024