



3-1/2 in. EMT Raintight Compression Coupling

By Raco
Catalog # 2954RT

3-1/2 in. EMT Raintight Compression Coupling



*Representative Image

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Marked with "Wet Location" for easy inspection
- cULus
- Available in trade sizes of 1/2 in. through 4 in.

General

Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Couplings
Material	Steel
UPC	050169501108

Dimensions

Dimensions	5.419 in x 4.585 in x 4.8 in
Height	4.8 in
Length	5.419 in
Trade Size	3-1/2 in
Weight	2.814 lb
Width	4.585 in

Certifications And Compliance

Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	392

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195970 - 2](#)
[Product Logo - Conduit](#)
[Sales Drawings - 2922RT](#)
[SDS - HCC SDS](#)
[Sell Sheets - Raintight Steel EMT Compression Fittings](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-2954RT-SPEC-EN | REV 6/2024