



4 in. Round Ceiling Rated Box, 1-1/2 in. Deep, Five 1/2 in. KO's

By Raco
Catalog # 296

4 in. Round Ceiling Rated Box, 1-1/2 in. Deep, Five 1/2 in. KO's



Features

- Constructed of pre-galvanized steel
- No protruding ground screw or fan mounting screws allows easy installation
- Steel cover protects wires from damage, paint, and drywall compound during installation
- Maximum support load for ceiling fans 70 lbs. and 150 lbs. for static light fixtures
- #10-32, 1 in. long ceiling fan screws provided and provision for #8-32 fixture mounting screw
- Easy to follow instructions and mounting hardware included
- Supplied with five 1/2 in. knockouts
- 1/2 in. side knockouts

General

| | |
|-------------------|----------------------|
| Bracket Type | No Bracket |
| Catalog Number | 296 |
| Ceiling Fan Rated | Yes |
| Drawn or Welded | Drawn |
| EU RoHS Indicator | Contact Manufacturer |
| Fixture Type | Ceiling;Light |
| Knockouts | 1/2 in |
| Material | Steel |
| Size | 4 in |
| Type | Box |
| UPC | 050169002964 |

Dimensions

| | |
|------------------|------------|
| Actual Depth | 2 in |
| Ceiling Fan Lbs. | 70 lb |
| Cubic Capacity | 15.8 cu.in |
| Depth | 1.5 in |
| Fixture Lbs. | 150 lb |
| Height | 4.25 in |
| Raised Ground | Yes |
| Weight | 0.819 lb |
| Width | 4.25 in |

Certifications And Compliance

Certified Listed UL Listed

Logistics

| | |
|-----------------|--------------|
| Carton Quantity | 8 |
| Packaging Type | No Packaging |
| Pallet Quantity | 1536 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Installation Manuals - Ceiling Box Installation Instructions](#)
[Sales Drawings - 296 Customer Drawing](#)
[SDS - HCC SDS](#)
[Sell Sheets - 4 in. Round Ceiling Fan-Rated Box](#)
[Sell Sheets - RACO® Ceiling Fan Boxes](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-296-SPEC-EN | REV 6/2024