



## 4 in. Round Ceiling Rated Box, 1-1/2 in. Deep, Five 1/2 in. KO's

By Raco  
Catalog # 296-1

4 in. Round Ceiling Rated Box, 1-1/2 in. Deep, Five 1/2 in. KO's



### Features

- Constructed of pre-galvanized steel
- No protruding ground screw or fan mounting screws allows easy installation
- Steel cover protects wires from damage, paint, and drywall compound during installation
- Maximum support load for ceiling fans 70 lbs. and 150 lbs. for static light fixtures
- #10-32, 1 in. long ceiling fan screws provided and provision for #8-32 fixture mounting screw
- Easy to follow instructions and mounting hardware included
- Supplied with five 1/2 in. knockouts
- 15.8 cu. in. capacity

### General

Bracket Type	No Bracket
Catalog Number	296-1
Ceiling Fan Rated	Yes
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Ceiling;Light
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Size	4 in
Type	Box
UPC	050169029619

### Dimensions

Actual Depth	1.563 in
Ceiling Fan Lbs.	70 lb
Cubic Capacity	15.8 cu.in
Depth	1.5 in
Fixture Lbs.	150 lb
Height	4 in
Raised Ground	Yes
Weight	0.735 lb
Width	4 in

### Certifications And Compliance

Certified Listed                      UL Listed

### Logistics

Carton Quantity	20
Packaging Type	Box
Pallet Quantity	1600

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Installation Manuals - Ceiling Box Installation Instructions](#)  
[Sales Drawings - 296](#)  
[Sales Drawings - RACO-drawn-steel-box-infographic](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - 4 in. Round Ceiling Fan-Rated Box](#)  
[Sell Sheets - RACO® Ceiling Fan Boxes](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-2961-SPEC-EN | REV 6/2024