



4 in. EMT Raintight Compression Connector, Insulated

By Raco
Catalog # [2966RT](#)



*Representative Image

4 in. EMT Raintight Compression Connector, Insulated

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insulated
- Marked with "Wet Location" for easy inspection
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- Installed knockout seal

General

Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel
UPC	050169501078

Dimensions

Dimensions	4.171 in x 5.3 in x 5.07 in
Height	5.07 in
Length	4.171 in
Trade Size	4 in
Weight	2.326 lb
Width	5.3 in

Certifications And Compliance

Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	343

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195970 - 2](#)
[Product Logo - Conduit](#)
[Sales Drawings - 2912RT](#)
[SDS - HCC_SDS](#)
[Sell Sheets - Raintight Steel EMT Compression Fittings](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2966RT-SPEC-EN | REV 6/2024