



3/8 in. 90 Degree Flex/AC Squeeze Connector, Insulated

By Raco
Catalog # 3201

3/8 in. 90 Degree Flex/AC Squeeze Connector, Insulated



*Representative Image

Features

- Rugged metallic construction ensures mechanical protection for the raceway
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

General

Catalog Number	3201
Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169032015

Dimensions

Dimensions	2.016 in x 1.375 in x 1.33 in
Height	1.33 in
Length	2.016 in
Trade Size	3/8 in
Weight	0.088 lb
Width	1.375 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	50
Pallet Quantity	20250

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - MC_BX_CONDUIT LOGO](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand