



3/4 in. 90 Degree Flex Double Bite Saddle Connector

By Raco
Catalog # 3203DB



3/4 in. 90 Degree Flex Double Bite Saddle Connector

Features

- Malleable iron and steel construction for added strength
- Available in 3/8 in. to 1 in. trade sizes
- Dual saddle clamp ensures proper conduit and cable connection for raceway
- Zinc plated for corrosion resistant installation
- Tri-head screw/clamp design - connectors can be installed by using a slotted, Phillips or Robertson head screwdriver
- Insulated throats on all DOUBLE BITE connectors provide maximum wire protection
- Additional sizes available

General

Conduit Type	Flexible Metal Conduit
Connector Type	Saddle
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169532034

Dimensions

Dimensions	2.5 in x 2.5 in x 1.375 in
Height	1.375 in
Length	2.5 in
Trade Size	3/4 in
Weight	0.375 lb
Width	2.5 in

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B
Nema Rating	NEMA FB-1

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	7680

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195966-1](#)
[Literature - Raco_Metal_Clad_Double_Bite_Selection_B74](#)
[Product Logo - MC_BX](#)
[SDS - HCC SDS](#)
[Sell Sheets - Double Bite Saddle Connectors](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-3203DB-SPEC-EN | REV 6/2024