



# 1 in. 90 Degree Flex Double Bite Saddle Connector

By Raco  
Catalog # 3204DB



1 in. 90 Degree Flex Double Bite Saddle Connector

## Features

- Malleable iron and steel construction for added strength
- Available in 3/8 in. to 1 in. trade sizes
- Dual saddle clamp ensures proper conduit and cable connection for raceway
- Zinc plated for corrosion resistant installation
- Tri-head screw/clamp design - connectors can be installed by using a slotted, Phillips or Robertson head screwdriver
- Insulated throats on all DOUBLE BITE connectors provide maximum wire protection
- Additional sizes available

## General

Conduit Type	Flexible Metal Conduit
Connector Type	Saddle
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169532041

## Dimensions

Dimensions	2.875 in x 2.813 in x 1.688 in
Height	1.688 in
Length	2.875 in
Trade Size	1 in
Weight	0.531 lb
Width	2.813 in

## Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B
Nema Rating	NEMA FB-1

## Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	5000

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - UL COC - E195966-1](#)
- [Literature - Raco\\_Metal\\_Clad\\_Double\\_Bite\\_Selection\\_B74](#)
- [Product Logo - MC\\_BX](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Double Bite Saddle Connectors](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
RACO-3204DB-SPEC-EN | REV 6/2024