



2 in. 90 Degree Flex Squeeze Connector, Insulated

By Raco
Catalog # 3208



2 in. 90 Degree Flex Squeeze Connector, Insulated

Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

General

Catalog Number	3208
Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169032084

Dimensions

Dimensions	6.797 in x 3.797 in x 4.53 in
Height	4.53 in
Length	6.797 in
Trade Size	2 in
Weight	3.125 lb
Width	3.797 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	600

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - MC_BX_CONDUIT LOGO](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)