



## 2-1/2 in. Flex Squeeze Connector, Insulated

By Raco  
Catalog # 3210



2-1/2 in. Flex Squeeze Connector, Insulated

### Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

### General

Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169032107

### Dimensions

Dimensions	7.563 in x 4.328 in x 5.25 in
Height	5.25 in
Length	7.563 in
Trade Size	2-1/2 in
Weight	3.652 lb
Width	4.328 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	360

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - MC\\_BX\\_CONDUIT LOGO](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-3210-SPEC-EN | REV 6/2024