



## 3-1/2 in. Flex Squeeze Connector, Insulated

By Raco  
Catalog # 3214



3-1/2 in. Flex Squeeze Connector, Insulated

### Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

### General

Catalog Number	3214
Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169032145

### Dimensions

Dimensions	11.234 in x 6.797 in x 7.5 in
Height	7.5 in
Length	11.234 in
Trade Size	3-1/2 in
Weight	11.276 lb
Width	6.797 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	84

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - MC\\_BX\\_CONDUIT LOGO](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand