



4 in. Flex Squeeze Connector, Insulated

By Raco
Catalog # 3216

4 in. Flex Squeeze Connector, Insulated

Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

General

Catalog Number	3216
Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169032169

Dimensions

Dimensions	12.344 in x 7.266 in x 8.625 in
------------	---------------------------------



Height	8.625 in
Length	12.344 in
Trade Size	4 in
Weight	14.508 lb
Width	7.266 in

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer cULus Listed
--	--------------------------------------

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	72

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - MC_BX_CONDUIT LOGO](#)
- [SDS - HCC SDS](#)
- [Specifications - 3216](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand