



## 4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Seven 1/2 in. KO's, Raised Ground, and Bar Hanger

By Raco  
Catalog # [324](#)



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Seven 1/2 in. KO's, Raised Ground, and Bar Hanger

### Features

- Included bar hanger is adjustable 16 -24 in.
- 10 lb. max load recommended on 24 in. center
- When used on 16 in. center, rated to support up to 50 lb. light fixture
- Fixture bar hanger allows box to be located anywhere along length of bar
- 4 in. x 1-1/2 in. deep
- Drawn steel construction with raised ground screw area
- Supplied with seven 1/2 in. knockouts
- Combination screw heads provide for faster installation
- 15.5 cu. in. capacity

### General

Bracket Type	No Bracket
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Size	4 in
Type	Box
UPC	050169003244
Wiring System	Conduit

### Dimensions

Actual Depth	2.132 in
Cubic Capacity	15.5 cu.in
Depth	1.5 in
Fixture Lbs.	10 lb
Height	3.563 in
Raised Ground	Yes
Weight	0.846 lb
Width	14.5 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1650

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Sales Drawings - RACO-drawn-steel-box-infographic](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-324-SPEC-EN | REV 6/2024