



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Two 1/2 in. KO's, AC/MC/Flex Clamps and Bar Hanger

By Raco
Catalog # 325



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Two 1/2 in. KO's, AC/MC/Flex Clamps and Bar Hanger

Features

- Included bar hanger is adjustable 16-24 in.
- 10 lb. max load recommended on 24 in. center
- When used on 16 in. center, rated to support up to 50 lb. light fixture
- Fixture bar hanger allows box to be located anywhere along length of bar
- Maximum support load for a static is 50 lbs. when supported 16 in. centers
- Cable clamps suitable for use with non-metallic sheathed cable
- Not suitable for ceiling fan installations
- 15.5 cu. in. capacity

General

Bracket Type	No Bracket
Ceiling Fan Rated	No
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	4 in
Type	Box
UPC	050169903254
Wiring System	Armored Cable/Metal Clad/MCI-A/Flex

Dimensions

Actual Depth	2.132 in
Cubic Capacity	15.5 cu.in
Depth	1.5 in
Fixture Lbs.	10 lb
Height	3.563 in
Raised Ground	No
Weight	0.998 lb
Width	14.5 in

Certifications And Compliance

Certified Listed cULus Listed

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1650

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-325-SPEC-EN | REV 6/2024