



3/8 in. Flex/MCI/MCI-A/AC Double Bite Saddle Connector, Insulated

By Raco
Catalog # 3301DB

3/8 in. Flex/MCI/MCI-A/AC Double Bite Saddle Connector,
Insulated



Features

- All steel construction ensures mechanical protection for raceways
- Available in 3/8 in. to 4 in. trade sizes
- Dual saddle clamp ensures proper conduit and cable connection for raceway
- Zinc plated for corrosion resistant installation
- Tri-head screw/clamp design - connectors can be installed by using a slotted, Phillips or Robertson head screwdriver
- Insulated throats on all DOUBLE BITE connectors provide maximum wire protection
- Additional sizes available

General

Conduit Type	Flexible Metal Conduit
Connector Type	Saddle
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel
UPC	050169533017

Dimensions

Dimensions	1.688 in x 1.25 in x 1.266 in
Height	1.266 in
Length	1.688 in
Trade Size	3/8 in
Weight	0.148 lb
Width	1.25 in

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B
Nema Rating	NEMA FB-1

Logistics

Carton Quantity	50
Pallet Quantity	24000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195966-1](#)
[Customer Notices - Prop65_Cancer](#)
[Literature - Raco_Metal_Clad_Double_Bite_Selection_B74](#)
[Product Logo - MC_BX](#)
[SDS - HCC SDS](#)
[Sell Sheets - Double Bite Saddle Connectors](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-3301DB-SPEC-EN | REV 6/2024