



1/2 in. Flex Straight Squeeze Connector, Insulated

By Raco
Catalog # 3302-8



1/2 in. Flex Straight Squeeze Connector, Insulated

Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

General

Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169330289

Dimensions

Dimensions	1.36 in x 1.25 in x 1.625 in
Height	1.625 in
Length	1.36 in
Trade Size	1/2 in
Weight	0.139 lb
Width	1.25 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7600

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand