



3/4 in. Flex/MCI/MCI-A/AC Double Bite Saddle Connector

By Raco
Catalog # 3303DB

3/4 in. Flex/MCI/MCI-A/AC Double Bite Saddle Connector

Features

- All steel construction ensures mechanical protection for raceways
- Available in 3/8 in. to 4 in. trade sizes
- Dual saddle clamp ensures proper conduit and cable connection for raceway
- Zinc plated for corrosion resistant installation
- Tri-head screw/clamp design - connectors can be installed by using a slotted, Phillips or Robertson head screwdriver
- Insulated throats on all DOUBLE BITE connectors provide maximum wire protection
- Additional sizes available

General

Catalog Number	3303DB
Conduit Type	Flexible Metal Conduit
Connector Type	Saddle
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel
UPC	050169533031

Dimensions

Dimensions	1.813 in x 1.438 in x 1.875 in
Height	1.875 in



*Representative Image

Length	1.813 in
Trade Size	3/4 in
Weight	0.172 lb
Width	1.438 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed
Industry Standard(s)	UL 514B
Nema Rating	NEMA FB-1

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	5760

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Certifications - UL COC - E195966-1](#)
[Customer Notices - Prop65_Cancer](#)
[Literature - Raco_Metal_Clad_Double_Bite_Selection_B74](#)
[Product Logo - MC_BX](#)
[SDS - HCC SDS](#)
[Sell Sheets - Double Bite Saddle Connectors](#)
[Specifications - 3303DB](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand