



# 1-1/4 in. Flex Straight Squeeze Connector, Insulated

By Raco  
Catalog # 3305



1-1/4 in. Flex Straight Squeeze Connector, Insulated

## Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

## General

Catalog Number	3305
Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169033050

## Dimensions

Dimensions	1.797 in x 2.063 in x 2.563 in
------------	--------------------------------

Height	2.563 in
Length	1.797 in
Trade Size	1-1/4 in
Weight	0.47 lb
Width	2.063 in

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	6750

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[SDS - HCC SDS](#)  
[Specifications - 3305](#)  
[Terms and Conditions - HCC Terms & Conditions](#)