



# 1-1/4 in. Flex Double Bite Saddle Connector

By Raco  
Catalog # 3305DB

1-1/4 in. Flex Double Bite Saddle Connector



\*Representative Image

## Features

- All steel construction ensures mechanical protection for raceways
- Available in 3/8 in. to 4 in. trade sizes
- Dual saddle clamp ensures proper conduit and cable connection for raceway
- Zinc plated for corrosion resistant installation
- Tri-head screw/clamp design - connectors can be installed by using a slotted, Phillips or Robertson head screwdriver
- Insulated throats on all DOUBLE BITE connectors provide maximum wire protection
- Additional sizes available

## General

Conduit Type	Flexible Metal Conduit
Connector Type	Saddle
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel
UPC	050169533055

## Dimensions

Dimensions	2.813 in x 2.125 in x 2.313 in
Height	2.313 in
Length	2.813 in
Trade Size	1-1/4 in
Weight	0.531 lb
Width	2.125 in

## Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B
Nema Rating	NEMA FB-1

## Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	2880

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Literature - Raco\\_Metal\\_Clad\\_Double\\_Bite\\_Selection\\_B74](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - Double Bite Saddle Connectors](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
RACO-3305DB-SPEC-EN | REV 6/2024