



2 in. Flex Straight Squeeze Connector, Insulated

By Raco
Catalog # 3308



*Representative Image

Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

General

Catalog Number	3308
Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169033081

Dimensions

Dimensions	2.75 in x 2.891 in x 3.344 in
------------	-------------------------------

Height	3.344 in
Length	2.75 in
Trade Size	2 in
Weight	1.082 lb
Width	2.891 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Customer Notices - Prop 65 Notice](#)
[SDS - HCC SDS](#)
[Specifications - 3308](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand