



3 in. Flex Double Bite Saddle Connector

By Raco
Catalog # 3312DB

3 in. Flex Double Bite Saddle Connector



*Representative Image

Features

- All steel construction ensures mechanical protection for raceways
- Available in 3/8 in. to 4 in. trade sizes
- Dual saddle clamp ensures proper conduit and cable connection for raceway
- Zinc plated for corrosion resistant installation
- Tri-head screw/clamp design - connectors can be installed by using a slotted, Phillips or Robertson head screwdriver
- Insulated throats on all DOUBLE BITE connectors provide maximum wire protection
- Additional sizes available

General

Catalog Number	3312DB
Conduit Type	Flexible Metal Conduit
Connector Type	Saddle
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel
UPC	050169533123

Dimensions

Dimensions	3.625 in x 4.25 in x 4.563 in
Height	4.563 in
Length	3.625 in
Trade Size	3 in
Weight	1.915 lb
Width	4.25 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
Industry Standard(s)	UL 514B
Nema Rating	NEMA FB-1

Logistics

Carton Quantity	1
Minimum Pack Quantity	1

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop65_Cancer](#)
[Literature - Raco_Metal_Clad_Double_Bite_Selection_B74](#)
[SDS - HCC SDS](#)
[Sell Sheets - Double Bite Saddle Connectors](#)
[Specifications - 3312DB](#)
[Terms and Conditions - HCC Terms & Conditions](#)