



3-1/2 in. Flex Double Bite Saddle Connector

By Raco
Catalog # 3314DB

3-1/2 in. Flex Double Bite Saddle Connector



*Representative Image

Features

- All steel construction ensures mechanical protection for raceways
- Available in 3/8 in. to 4 in. trade sizes
- Dual saddle clamp ensures proper conduit and cable connection for raceway
- Zinc plated for corrosion resistant installation
- Tri-head screw/clamp design - connectors can be installed by using a slotted, Phillips or Robertson head screwdriver
- Insulated throats on all DOUBLE BITE connectors provide maximum wire protection
- Additional sizes available

General

Conduit Type	Flexible Metal Conduit
Connector Type	Saddle
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel
UPC	050169533147

Dimensions

Dimensions	3.938 in x 4.75 in x 5 in
Height	5 in
Length	3.938 in
Trade Size	3-1/2 in
Weight	2.25 lb
Width	4.75 in

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B
Nema Rating	NEMA FB-1

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	480

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop65_Cancer](#)
[Literature - Raco_Metal_Clad_Double_Bite_Selection_B74](#)
[SDS - HCC SDS](#)
[Sell Sheets - Double Bite Saddle Connectors](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-3314DB-SPEC-EN | REV 6/2024