



## 4 in. Flex Double Bite Saddle Connector

By Raco  
Catalog # 3316DB

4 in. Flex Double Bite Saddle Connector



\*Representative Image

### Features

- All steel construction ensures mechanical protection for raceways
- Available in 3/8 in. to 4 in. trade sizes
- Dual saddle clamp ensures proper conduit and cable connection for raceway
- Zinc plated for corrosion resistant installation
- Tri-head screw/clamp design - connectors can be installed by using a slotted, Phillips or Robertson head screwdriver
- Insulated throats on all DOUBLE BITE connectors provide maximum wire protection
- Additional sizes available

### General

Conduit Type	Flexible Metal Conduit
Connector Type	Saddle
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel
UPC	050169533161

### Dimensions

Dimensions	4.063 in x 5.188 in x 5.5 in
Height	5.5 in
Length	4.063 in
Trade Size	4 in
Weight	2.633 lb
Width	5.188 in

### Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B
Nema Rating	NEMA FB-1

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	480

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Customer Notices - Prop 65 Notice](#)  
[Literature - Raco\\_Metal\\_Clad\\_Double\\_Bite\\_Selection\\_B74](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - Double Bite Saddle Connectors](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-3316DB-SPEC-EN | REV 6/2024