



## 1/2 in. Liquidtight Straight Connector, Uninsulated

By Raco  
Catalog # 3402-8



1/2 in. Liquidtight Straight Connector, Uninsulated

\*Representative Image

### Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

### General

Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel/Malleable Iron
UPC	050169340288

### Dimensions

Dimensions	1.738 in x 1.173 in x 1.349 in
Height	1.349 in
Length	1.738 in
Trade Size	1/2 in
Weight	0.172 lb
Width	1.173 in

### Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Hazardous Rating(s)	Class I, Division 2
	Class II Division 1 & 2
	Class III, Division 1 & 2
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	15
Minimum Pack Quantity	15
Pallet Quantity	8190

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - LT COND](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-34028-SPEC-EN | REV 6/2024