



# 1/2 in. Liquidtight Straight Connector, Uninsulated

By Raco  
Catalog # 3402DC

1/2 in. Liquidtight Straight Connector, Uninsulated



\*Representative Image

## Features

- Diecast zinc construction
- Noninsulated
- Patented split gland-ring assures a perfect seal, preventing pullouts
- cULus
- Available in trade sizes 3/8 in. through 2 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

## General

Catalog Number	3402DC
Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Die Cast Zinc
UPC	050169980057

## Dimensions

Dimensions	1.407 in x 1.29 in x 1.383 in
Height	1.383 in

Length	1.407 in
Trade Size	1/2 in
Weight	0.135 lb
Width	1.29 in

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed

## Logistics

Carton Quantity	200
Pallet Quantity	20000

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3402DC Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Die Cast LiquidTight Fittings](#)
- [Specifications - 3402DC](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)