



1-1/4 in. Liquidtight Straight Connector, Uninsulated

By Raco
Catalog # 3405DC

1-1/4 in. Liquidtight Straight Connector, Uninsulated



*Representative Image

Features

- Diecast zinc construction
- Noninsulated
- Patented split gland-ring assures a perfect seal, preventing pullouts
- cULus
- Available in trade sizes 3/8 in. through 2 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Die Cast Zinc
UPC	050169980088

Dimensions

Dimensions	1.875 in x 2.273 in x 2.419 in
Height	2.419 in
Length	1.875 in
Trade Size	1-1/4 in
Weight	0.507 lb
Width	2.273 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	2940

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)

[Product Logo - LT COND](#)

[Sales Drawings - 3401DC](#)

[SDS - HCC SDS](#)

[Sell Sheets - Die Cast LiquidTight Fittings](#)

[Terms and Conditions - HCC Terms & Conditions](#)

[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-3405DC-SPEC-EN | REV 6/2024