



1-1/2 in. Liquidtight Straight Connector, Uninsulated

By Raco
Catalog # 3406



*Representative Image

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3406
Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel/Malleable Iron
UPC	050169034064

Dimensions

Dimensions	2.813 in x 2.813 in x 2.438 in
Height	2.438 in
Length	2.813 in

Trade Size	1-1/2 in
Weight	0.85 lb
Width	2.813 in

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	2520

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Product Logo - LT COND](#)
[Sales Drawings - 3406 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 3406](#)
[Terms and Conditions - HCC Terms & Conditions](#)