



# 2 in. Liquidtight Straight Connector, Uninsulated

By Raco  
Catalog # 3408

2 in. Liquidtight Straight Connector, Uninsulated

### Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

### General

Catalog Number	3408
Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel/Malleable Iron
UPC	050169034088

### Dimensions

Dimensions	3.5 in x 3.5 in x 2.75 in
Height	2.75 in
Length	3.5 in
Trade Size	2 in



\*Representative Image

Weight	1.46 lb
Width	3.5 in

### Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1500

### Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3408 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 3408](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)