



## 1/2 in. 90 Degree Liquidtight Connector, Uninsulated

By Raco  
Catalog # 3422DC



1/2 in. 90 Degree Liquidtight Connector, Uninsulated

\*Representative Image

### Features

- Diecast zinc construction
- Noninsulated
- Patented split gland-ring assures a perfect seal, preventing pullouts
- cULus
- Available in trade sizes 3/8 in. through 2 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

### General

Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Die Cast Zinc
UPC	050169980125

### Dimensions

Dimensions	2.545 in x 1.29 in x 2.267 in
Height	2.267 in
Length	2.545 in
Trade Size	1/2 in
Weight	0.191 lb
Width	1.29 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	100
Minimum Pack Quantity	25
Pallet Quantity	10000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - LT COND](#)  
[Sales Drawings - 3421DC](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - Die Cast LiquidTight Fittings](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-3422DC-SPEC-EN | REV 6/2024