



1 in. 90 Degree Liquidtight Connector, Uninsulated

By Raco
Catalog # 3424-8



1 in. 90 Degree Liquidtight Connector, Uninsulated

*Representative Image

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel/Malleable Iron
UPC	050169342480

Dimensions

Dimensions	3.25 in x 1.719 in x 2.9 in
Height	2.9 in
Length	3.25 in
Trade Size	1 in
Weight	0.585 lb
Width	1.719 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Hazardous Rating(s)	Class I, Division 2
	Class II Division 1 & 2
	Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	2730

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Product Logo - LT COND](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-34248-SPEC-EN | REV 6/2024