



1-1/2 in. 90 Degree Liquidtight Connector, Uninsulated

By Raco
Catalog # [3426](#)

1-1/2 in. 90 Degree Liquidtight Connector, Uninsulated

Features

- Patented split gland-ring is designed to slip onto the conduit quickly and to grip the jacket of the conduit, speeding installation, assuring a perfect seal and preventing pullouts
- RACO liquidtight connectors may be easily disassembled and reused after years of service
- Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening
- Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground
- All steel/iron components are zinc electroplated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- 3/8 in. to 1 in. Steel, 1-1/4 in. to 4 in. Malleable Iron bodies and nuts
- Additional sizes available

General

Catalog Number	3426
EU RoHS Indicator	Yes
Material	Steel/Malleable Iron
UPC	050169034262

Dimensions

Dimensions	2.813 in x 2.813 in x 5.063 in
Height	5.063 in



*Representative Image

Length	2.813 in
Trade Size	1.5 in
Weight	1.36 lb
Width	2.813 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Product Logo - LT COND](#)
[Sales Drawings - 3426 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 3426](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand