



4 in. 90 Degree Liquidtight Connector, Uninsulated

By Raco
Catalog # 3436



4 in. 90 Degree Liquidtight Connector, Uninsulated

*Representative Image

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3436
Conduit Type	Liquidtight
EU RoHS Indicator	Yes
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel/Malleable Iron
UPC	050169034361

Dimensions

Dimensions	6.063 in x 6.063 in x 11.313 in
Height	11.313 in
Length	6.063 in
Trade Size	4 in
Weight	13.95 lb
Width	6.063 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Hazardous Rating(s)	Class I, Division 2
	Class II Division 1 & 2
	Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	96

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - LT COND](#)
[Sales Drawings - 3436 Customer Drawing](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-3436-SPEC-EN | REV 6/2024