



3/8 in. 45 Degree Liquidtight Connector, Uninsulated

By Raco
Catalog # 3441



3/8 in. 45 Degree Liquidtight Connector, Uninsulated

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

| | |
|--------------------------|----------------------|
| Conduit Type | Liquidtight |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Wet Location |
| Fitting Type | Connectors |
| Insulation Type | Uninsulated |
| Material | Steel/Malleable Iron |
| UPC | 050169034415 |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 1.188 in x 1.188 in x 2.375 in |
| Height | 2.375 in |
| Length | 1.188 in |
| Trade Size | 3/8 in |
| Weight | 0.204 lb |
| Width | 1.188 in |

Certifications And Compliance

| | |
|----------------------|-----------------------------|
| Certified Listed | • UL Listed |
| | • CSA Certified |
| Hazardous Rating(s) | • Class I, Division 2 |
| | • Class II Division 1 & 2 |
| | • Class III, Division 1 & 2 |
| Industry Standard(s) | UL 514B |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 25 |
| Minimum Pack Quantity | 25 |
| Pallet Quantity | 10000 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - LT COND](#)
[Sales Drawings - 3441](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-3441-SPEC-EN | REV 6/2024