



3/4 in. 45 Degree Liquidtight Connector, Uninsulated

By Raco
Catalog # 3443



3/4 in. 45 Degree Liquidtight Connector, Uninsulated

*Representative Image

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3443
Conduit Type	Liquidtight
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel/Malleable Iron
UPC	050169034439

Dimensions

Dimensions	1.625 in x 1.625 in x 2.813 in
Height	2.813 in
Length	1.625 in
Trade Size	3/4 in

Weight	0.348 lb
Width	1.625 in

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	5000

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3443 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 3443](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand