



1 in. 45 Degree Liquidtight Connector, Uninsulated

By Raco
Catalog # 3444

1 in. 45 Degree Liquidtight Connector, Uninsulated



Features

-
-
-
-
-
-
-

General

Catalog Number	3444
Conduit Type	Liquidtight
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel/Malleable Iron
UPC	050169034446

Dimensions

Dimensions	1.938 in x 1.938 in x 3.375 in
Height	3.375 in
Length	1.938 in
Trade Size	1 in
Weight	0.535 lb

Width 1.938 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3200

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3444 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 3444](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)