



2 in. 45 Degree Liquidtight Connector, Uninsulated

By Raco
Catalog # 3448

2 in. 45 Degree Liquidtight Connector, Uninsulated

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3448
Conduit Type	Liquidtight
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel/Malleable Iron
UPC	050169034484

Dimensions

Dimensions	3.5 in x 3.5 in x 4.938 in
Height	4.938 in
Length	3.5 in
Trade Size	2 in



Weight	1.98 lb
Width	3.5 in

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	800

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3448 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 3448](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand