



1/2 in. Liquidtight Straight Connector, Insulated

By Raco
Catalog # 3512DC

1/2 in. Liquidtight Straight Connector, Insulated



*Representative Image

Features

- Diecast zinc construction
- Insulated
- cULus
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Conduit Type	Flexible Metal Conduit
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Die Cast Zinc
UPC	050169980194

Dimensions

Dimensions	1.487 in x 1.29 in x 1.383 in
Height	1.383 in
Length	1.487 in
Trade Size	1/2 in
Weight	0.136 lb
Width	1.29 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	200
Pallet Quantity	20000

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3511DC](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Die Cast LiquidTight Fittings](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-3512DC-SPEC-EN | REV 6/2024