



1/2 in. Liquidtight Straight Connector, Insulated

By Raco
Catalog # 3512RAC

1/2 in. Liquidtight Straight Connector, Insulated

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Insulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3512RAC
Conduit Type	Flexible Metal Conduit
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	3512RAC
UPC	050169035122

Dimensions

Dimensions	1.313 in x 1.313 in x 1.813 in
Height	1.813 in
Length	1.313 in



*Representative Image

Trade Size	1/2 in
Weight	0.172 lb
Width	1.313 in

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	200
Pallet Quantity	12000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Product Logo - LT COND](#)
[Sales Drawings - 3512RAC Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 3512RAC](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand