



3/4 in. Liquidtight Straight Connector, Insulated with Ground Lug

By Raco
Catalog # 3513-3

3/4 in. Liquidtight Straight Connector, Insulated with Ground Lug

Features

- Steel construction ensures mechanical protection
- All metallic components are zinc electroplated for added corrosion protection
- Insulated with ground lug
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3513-3
Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	3513-3
UPC	050169351338

Dimensions

Dimensions	1.484 in x 1.406 in x 1.406 in
Height	1.406 in
Length	1.484 in
Trade Size	3/4 in
Weight	0.249 lb
Width	1.406 in



*Representative Image

Electrical Ratings

Grounding Wire Capacity Maximum	#4 STR
Grounding Wire Capacity Minimum	#14 SOL

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Certifications - UL COC-E195975-4](#)
[Product Logo - LT COND](#)
[Sales Drawings - 35133 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 35133](#)
[Terms and Conditions - HCC Terms & Conditions](#)