



## 3/4 in. Liquidtight Straight Connector, Insulated

By Raco  
Catalog # 3513DC

3/4 in. Liquidtight Straight Connector, Insulated



\*Representative Image

### Features

- Diecast zinc construction
- Insulated
- cULus
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

### General

Conduit Type	Flexible Metal Conduit
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Die Cast Zinc
UPC	050169980200

### Dimensions

Dimensions	1.515 in x 1.575 in x 1.692 in
Height	1.692 in
Length	1.515 in
Trade Size	3/4 in
Weight	0.199 lb
Width	1.575 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	100
Minimum Pack Quantity	25
Pallet Quantity	10000

### Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3511DC](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Die Cast LiquidTight Fittings](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-3513DC-SPEC-EN | REV 6/2024