



# 1-1/4 in. Liquidtight Straight Connector, Insulated with Ground Lug

By Raco  
Catalog # 3515-3

1-1/4 in. Liquidtight Straight Connector, Insulated with Ground Lug

### Features

- Malleable iron construction ensures mechanical protection
- All metallic components are zinc electroplated for added corrosion protection
- Insulated with ground lug
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

### General

Catalog Number	3515-3
Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169351536

### Dimensions

Dimensions	1.875 in x 2.188 in x 2.188 in
Height	2.188 in
Length	1.875 in
Trade Size	1-1/4 in
Weight	0.688 lb
Width	2.188 in



\*Representative Image

### Electrical Ratings

Grounding Wire Capacity	#4 STR
Maximum	
Grounding Wire Capacity	#14 SOL
Minimum	

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	2940

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Certifications - UL COC-E195975-4](#)  
[Product Logo - LT COND](#)  
[Sales Drawings - 35153 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Specifications - 35153](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand