



2-1/2 in. Liquidtight Straight Connector, Insulated with Ground Lug

By Raco
Catalog # [3520-3](#)



2-1/2 in. Liquidtight Straight Connector, Insulated with Ground Lug

Features

- Malleable iron construction ensures mechanical protection
- All metallic components are zinc electroplated for added corrosion protection
- Insulated with ground lug
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169352038

Dimensions

Dimensions	3.313 in x 3.625 in x 3.625 in
Height	3.625 in
Length	3.313 in
Trade Size	2-1/2 in
Weight	3.355 lb
Width	3.625 in

Electrical Ratings

Grounding Wire Capacity Maximum	#1/0 STR
Grounding Wire Capacity Minimum	#14 SOL

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	432

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC-E195975-4](#)
[Product Logo - LT COND](#)
[Sales Drawings - 3520-3](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-35203-SPEC-EN | REV 6/2024