



# 3-1/2 in. Liquidtight Straight Connector, Insulated with Ground Lug

By Raco  
Catalog # [3524-3](#)



\*Representative Image

3-1/2 in. Liquidtight Straight Connector, Insulated with Ground Lug

## Features

- Malleable iron construction ensures mechanical protection
- All metallic components are zinc electroplated for added corrosion protection
- Insulated with ground lug
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

## General

Catalog Number	3524-3
Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169352434

## Dimensions

Dimensions	3.625 in x 3.969 in x 3.969 in
Height	3.969 in
Length	3.625 in
Trade Size	3-1/2 in
Weight	5.24 lb
Width	3.969 in

## Electrical Ratings

Grounding Wire Capacity Maximum	#250 MCM
Grounding Wire Capacity Minimum	#6 STR

## Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	294

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Certifications - UL COC-E195975-4](#)  
[Product Logo - LT COND](#)  
[Sales Drawings - 35243 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Specifications - 35243](#)  
[Terms and Conditions - HCC Terms & Conditions](#)