



4 in. Liquidtight Straight Connector, Insulated with Ground Lug

By Raco
Catalog # 3526-3

4 in. Liquidtight Straight Connector, Insulated with Ground Lug



*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- All metallic components are zinc electroplated for added corrosion protection
- Insulated with ground lug
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3526-3
Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	3526-3
UPC	050169352632

Dimensions

Dimensions	3.625 in x 5.547 in x 5.36 in
Height	5.36 in
Length	3.625 in
Trade Size	4 in
Weight	6.177 lb

Width 5.547 in

Electrical Ratings

Grounding Wire Capacity Maximum	#250 MCM
Grounding Wire Capacity Minimum	#6 STR

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	1
Minimum Pack Quantity	1

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC-E195975-4](#)
[Product Logo - LT COND](#)
[Sales Drawings - 35263 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 3526-3](#)
[Terms and Conditions - HCC Terms & Conditions](#)