



## 4 in. Liquidtight Straight Connector, Insulated with Ground Lug

By Raco  
Catalog # 3526-3

4 in. Liquidtight Straight Connector, Insulated with Ground Lug



\*Representative Image

### Features

- Malleable iron construction ensures mechanical protection
- All metallic components are zinc electroplated for added corrosion protection
- Insulated with ground lug
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

### General

Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	3526-3
UPC	050169352632

### Dimensions

Dimensions	3.625 in x 5.547 in x 5.36 in
Height	5.36 in
Length	3.625 in
Trade Size	4 in
Weight	6.177 lb
Width	5.547 in

### Electrical Ratings

Grounding Wire Capacity Maximum	#250 MCM
Grounding Wire Capacity Minimum	#6 STR

### Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Hazardous Rating(s)	Class I, Division 2
	Class II Division 1 & 2
	Class III, Division 1 & 2
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	294

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC-E195975-4](#)  
[Product Logo - LT COND](#)  
[Sales Drawings - 3526-3](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-35263-SPEC-EN | REV 6/2024