



# 1/2 in. 90 Degree Liquidtight Connector, Insulated

By Raco  
Catalog # 3542DC



1/2 in. 90 Degree Liquidtight Connector, Insulated

\*Representative Image

## Features

- Diecast zinc construction
- Insulated
- Patented split gland-ring assures a perfect seal, preventing pullouts
- cULus
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

## General

Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Die Cast Zinc
UPC	050169980262

## Dimensions

Dimensions	2.545 in x 1.29 in x 2.347 in
Height	2.347 in
Length	2.545 in
Trade Size	1/2 in
Weight	0.192 lb
Width	1.29 in

## Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

## Logistics

Carton Quantity	100
Minimum Pack Quantity	25
Pallet Quantity	10000

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Engineering Drawing - 142651](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3541DC](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Die Cast LiquidTight Fittings](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-3542DC-SPEC-EN | REV 6/2024