



3/4 in. 90 Degree Liquidtight Connector,
Insulated

By RACO
Catalog # [3543](#)



3/4 in. 90 Degree Liquidtight Connector, Insulated

*Representative Image

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Insulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

Specifications

Buy American Compliant Certified Listed	Contact Manufacturer • UL Listed • CSA Certified
Environmental Conditions	Wet Location
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 514B
Hazardous Rating(s)	• Class I, Division 2 • Class II Division 1 & 2 • Class III, Division 1 & 2

Dimensions

Package Height	4.750 in
Length	2.875 in
Trade Size	3/4 in
Package Weight	10.583 lb.

Package Length	8.000 in
Package Width	7.188 in
Weight	0.37 lb.
Height	2.5 in
Width	1.141 in
Dimensions	2.875 in x 1.141 in x 2.5 in

General

Conduit Type	Liquidtight
Product Family	Liquidtight
Insulation Type	Insulated
Fitting Type	Connectors
Product Type	Commercial Fittings
UPC	050169035436
Material	Steel/Malleable Iron

Logistics

Minimum Pack Quantity	25
Pallet Quantity	6000
Carton Quantity	100

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)