



# 3/4 in. 90 Degree Liquidtight Connector, Insulated with Ground Lug

By Raco  
Catalog # 3543-3

3/4 in. 90 Degree Liquidtight Connector, Insulated with Ground Lug

## Features

- Malleable iron construction of the body and steel nut
- All metallic components are zinc electroplated for added corrosion protection
- Malleable iron castings mate with other components perfectly without strain or distortion
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

## General

Catalog Number	3543-3
Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169354339

## Dimensions

Dimensions	2.92 in x 1.406 in x 2.423 in
------------	-------------------------------



\*Representative Image

Height	2.423 in
Length	2.92 in
Trade Size	3/4 in
Weight	0.446 lb
Width	1.406 in

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	3750

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Certifications - UL COC-E195975-4](#)  
[Product Logo - LT COND](#)  
[SDS - HCC SDS](#)  
[Specifications - 35433](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand