



3/4 in. 90 Degree Liquidtight Connector, Insulated

By Raco
Catalog # 3543-8



3/4 in. 90 Degree Liquidtight Connector, Insulated

*Representative Image

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Insulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

| | |
|--------------------------|----------------------|
| Conduit Type | Liquidtight |
| EU RoHS Indicator | Contact Manufacturer |
| Environmental Conditions | Wet Location |
| Fitting Type | Connectors |
| Insulation Type | Insulated |
| Material | Steel/Malleable Iron |
| UPC | 050169354384 |

Dimensions

| | |
|------------|------------------------------|
| Dimensions | 2.875 in x 1.141 in x 2.5 in |
| Height | 2.5 in |
| Length | 2.875 in |
| Trade Size | 3/4 in |
| Weight | 0.37 lb |
| Width | 1.141 in |

Certifications And Compliance

| | |
|----------------------|---------------------------|
| Certified Listed | UL Listed |
| | CSA Certified |
| Hazardous Rating(s) | Class I, Division 2 |
| | Class II Division 1 & 2 |
| | Class III, Division 1 & 2 |
| Industry Standard(s) | UL 514B |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 10 |
| Minimum Pack Quantity | 10 |
| Pallet Quantity | 5460 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - LT COND](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-35438-SPEC-EN | REV 6/2024