



# 3/4 in. 90 Degree Liquidtight Connector, Insulated

By Raco  
Catalog # 3543DC



\*Representative Image

## Features

- Diecast zinc construction
- Insulated
- Patented split gland-ring assures a perfect seal, preventing pullouts
- cULus
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

## General

Catalog Number	3543DC
Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Die Cast Zinc
UPC	050169980279

## Dimensions

Dimensions	2.653 in x 1.575 in x 2.521 in
Height	2.521 in

Length	2.653 in
Trade Size	3/4 in
Weight	0.248 lb
Width	1.575 in

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed

## Logistics

Carton Quantity	100
Minimum Pack Quantity	25
Pallet Quantity	4500

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3543DC Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Die Cast LiquidTight Fittings](#)
- [Specifications - 3543DC](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)